



Designation: 18760

Battery Requirement: 3 x D

Bulb required: 6pcs Luxeon Mid-power cool white LED

Luminous intensity: High: 280 lm or 42 cd
Medium: 110 lm or 16 cd
Low: 32 lm or 5 cd

Range: High 13 m / Medium 8 m / Low 4.5 m
(calculated distance at maximum luminous intensity with an illuminance of 0.25lux).

Weight: 622g (without batteries).

Material: PA (Polyamide)
PC (Polycarbonate)
TPE (Thermoplastic Elastome)

All contact parts made of bronze or nickel plated steel.

Dimensions (mm):

A	215
B	94
C	102

Run Time: 40 hours with VARTA HE for High mode
100 hours with VARTA HE for Medium mode
280 hours with VARTA HE for Low mode

Features (Technical)

- 6pcs Luxeon Mid-power cool white LED
- IC control Push switch (High/Medium/Low/Off)
- 4.6 meters (15 feet) impact resistant
- IPX7 water proof
- Ambidextrous handle can be flipped up from either side
- Integrated hook in lantern base
- Extra thick housing & over mould rubber for maximum durability
- Passed extreme temperature shock test
- 10,000 Switch cycle life