

**AL-60SP12** (Artikel-Nr. 710146-07)

## EKULIT


**SPECIFICATIONS:**

TYPE	UNIT	AL-60SP12
• Min. Sound Output at 10cm	dB	85
Rated Voltage	V <sub>DC</sub>	12
Operating Voltage	V <sub>DC</sub>	8~15
Resonant Frequency	Hz	2.300±400
• Max. Current Consumption	mA	30
Operating Temperature	°C	-20~+70
Storage Temperature	°C	-30~+80
Weight	g	2

• Value applying at rated voltage DC

**DIMENSIONS :**

(Unit: mm)



**Frequency response:**

