

Technical datasheet: FT-27T-4.0B1-471

Specifications:

Resonant Frequency	4.0kHz \pm 0.5kHz
Max Resistance (Zr)	500 Ω
Capacitance	20000nF \pm 30%nF

Dimensions:

Type B: (D: \varnothing 27mm, d: \varnothing 20mm, T: 0.42mm, t: 0.20mm)

