

Technical datasheet: FT-31T-1.3A1-472

Specifications:

Resonant Frequency	1.3kHz \pm 0.5kHz
Max Resistance (Zr)	500 Ω
Capacitance	50000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 31mm, d: \varnothing 20mm, T: 0.23mm, t: 0.10mm)

