

## Data Sheet

---

### Piezo Element, FT-35T-2.6A1-K475

#### SPECIFICATION

##### 1. SCOPE

This specification is applied to the piezo-element.

##### 2. SPECIFICATION

(at 25 °C)

2.1 Resonant Frequency	:	2.6 ± 0.5 KHz
2.2 Resonant Resistance	:	300 Ω max
2.3 Capacitance	:	30000 pF ± 30% at 100 Hz
2.4 Input Voltage	:	30 V <sub>p-p</sub> max
2.5 Operating Temperature	:	-20 ~ +50 °C
2.6 Storage Temperature	:	-20 ~ +60 °C
3. DIMENSION	:	as per figure

