

Technical datasheet: FT-50T-1.9A1-K480

Specifications:

Resonant Frequency	1.9kHz \pm 0.5kHz
Max Resistance (Zr)	800 Ω
Capacitance	70000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 50mm, d: \varnothing 25mm, T: 0.23mm, t: 0.10mm)

