

Technical datasheet: FT-50T-3.0A1-481

Specifications:

Resonant Frequency	5.0kHz \pm 0.5kHz
Max Resistance (Zr)	500 Ω
Capacitance	30000nF \pm 30%nF

Dimensions:

Type A: (D: \varnothing 50mm, d: \varnothing 25mm, T: 0.43mm, t: 0.20mm)

