

# Technical datasheet: FT-20T-4.0A1-465

## Specifications:

Resonant Frequency	4.0kHz $\pm$ 0.5kHz
Max Resistance (Zr)	300 $\Omega$
Capacitance	30000nF $\pm$ 30%nF

## Dimensions:

Type A: (D:  $\varnothing$ 20mm, d:  $\varnothing$ 15mm, T: 0.26mm, t: 0.15mm)

