

Technical datasheet: KPMB-G2206L-K6405

Specifications:

Operating Temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Rated Voltage	6VDC
Operating Voltage	4V~8VDC
Max. Rated Current	30mA
Resonant Frequency	400Hz \pm 100Hz
Min SPL	75dB at 6VDC/20cm
Response Time	50ms
Tone Nature	Continues
Weight	10g
Case Material/Color	ABS/White

Dimensions:

