

## Technical datasheet: KPMB-G2212L-K6406

### Specifications:

Operating Temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Rated Voltage	12VDC
Operating Voltage	9V~15VDC
Max.Rated Current	30mA
Resonant Frequency	400±100Hz
Min SPL	75dB at 12VDC/20cm
Response Time	50ms
Tone Nature	Continues
Weight	10g
Case Material/Color	ABS/White

### Dimensions:

