

Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Double-level terminal block, Connection method: Fast/plug-in connection, Cross section: 0.25 mm² - 1.5 mm², Width: 5.2 mm, Color: blue, Mounting: NS 35/7,5, NS 35/15 / Ex data new / /

Product Features

- ✓ Ground terminal blocks of the same shape are available
- ✓ Tested for railway applications

Key commercial data

package_quantity	50
GTIN	4017918975852

Technical data

General

Number of levels	2
Number of connections	4
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I _N	17.5 A
Nominal voltage U _N	500 V
Open side panel	ja

Dimensions

Width	5.2 mm
-------	--------

Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

Technical data

Dimensions

Length	87.8 mm
Height NS 35/7,5	49.9 mm
Height NS 35/15	57.4 mm

Connection data

Conductor cross section solid min.	0.25 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.25 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	16
Connection method	Fast/plug-in connection
Internal cylindrical gage	A3
Material wire insulation	PVC / PE

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

approvals

CSA / UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

CSA 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	10 A	10 A	5 A
mm²/AWG/kcmil	24-16	24-16	24-16

UL Recognized 				
Usegroups	B	C	D	
Nominal voltage UN	300 V	300 V	600 V	600 V
Nominal current IN	10 A	10 A	5 A	10 A
mm²/AWG/kcmil	24-16	24-16	24-16	24-16

cUL Recognized 				
Usegroups	B	C	D	
Nominal voltage UN	300 V	300 V	600 V	600 V
Nominal current IN	10 A	10 A	5 A	10 A
mm²/AWG/kcmil	24-16	24-16	24-16	24-16

GOST 			
---	--	--	--

			
---	--	--	--

cULus Recognized 			
---	--	--	--

accessories

End cover

Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

D-QTTCB 1,5/2P - 3206306



DP PS-5 - 3036725



Test plug terminal block

PS-4/E - 3036709



PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

PAI-4-FIX-5/6 BN - 3035981



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



Partition plate

ATP-QTTCB - 3206238



Coding element

PC - 3040588



Screwdriver tools

Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

SZF 1-0,6X3,5 - 1204517



Flange

QTTCB 1,5/ 2P-F - 3061185



Bridge

FBS 2-5 - 3030161



FBS 3-5 - 3030174



FBS 4-5 - 3030187



Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

FBS 5-5 - 3030190



FBS 10-5 - 3030213



FBS 20-5 - 3030226



FBS 50-5 - 3038930



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Terminal marking

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



Labeled terminal marker

Double-level terminal block - QTTCB 1,5/ 2P BU - 3050206

accessories

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



Drawings

Circuit diagram



