

Cover plate - HC-D 15-AP-GY - 1660342

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON cover plate, for wall cutouts of type D15, 3.5 mm thick, gray

The illustration shows a version of the product

Key commercial data

package_quantity	10
GTIN	4017918021986

Technical data

Dimensions

Length	87 mm
Height	3.5 mm
Hole diameter	4.5 mm
Width	40 mm
Drill hole distance, horizontal	70 mm
Drill hole distance, vertical	17.5 mm

General

Note	For wall cutouts of type D15
Material	PA
Inflammability class according to UL 94	HB
Color	gray
Design	D15

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

Cover plate - HC-D 15-AP-GY - 1660342

classifications

ETIM

ETIM 3.0	EC002310
ETIM 4.0	EC000886
ETIM 5.0	EC002314

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

approvals

GOST /

Approval details

GOST 
--

Drawings

Dimensioned drawing



