

Cable gland - HC-M-KV-M20(11-16) - 1645998

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Metal screw connection up to 5 bar, thread length: 6 mm, cable diameter: 11 - 16 mm, WAF 27, screw connection: M20

Key commercial data

package_quantity	25
GTIN	4017918941260

Technical data

Dimensions

Wrench size, union nut	27 mm
Wrench size, support	27 mm
Length of the connecting thread	6 mm
External cable diameter	11 mm ... 16 mm
Conductor sealing range	11.00 mm ... 16.00 mm

Ambient conditions

Degree of protection	IP68, to 5 bar
Degree of protection	IP68 (Up to 5 bar)
Ambient temperature (operation)	-20 °C ... 100 °C

General

Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
Material, O-ring	NBR
Thread type on connection side	M20
Tightening torque, union nut	7.50 Nm

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109

Cable gland - HC-M-KV-M20(11-16) - 1645998

classifications

eCl@ss

eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Drawings

Dimensioned drawing

Dimensional drawing