

Marker for terminal blocks - UC-TM 6 PL-60 - 0828512

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

Key commercial data

package_quantity	60
GTIN	4046356556095

Technical data

Dimensions

Width (a)	6 mm
-----------	------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	80
Number of individual labels per row	10

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

Marker for terminal blocks - UC-TM 6 PL-60 - 0828512

classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

P1 UC-MAG 1 - 5146079



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>