


接线表 Wiring Table

IDC	DB9M
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9



Screw

技术要求

1. 环境温度: -25° C~+85° Temperature
2. 额定电流: 1.5A AC, DC Rating Current
3. 额定电压: 36 V AC, DC Rating Voltage
4. 绝缘电阻: ≥1000MΩ Insulation Resistance
5. 接触电阻: ≤0.02Ω Contact Resistance
6. 耐压: 750V AC/MIN Pressure
7. 机械寿命: ≥5000次 Life Time
8. 拉力 (导线与端子之间): >3.0Kkf
Pull Strength (Between cable and terminal)

Tolerance Table

未注公差见下表:

X	±5	X'	±3°
.X	±2	.X'	±2°
.XX	±0.25		

5	Blue DB9M Terminal 9P Male	PCS	1
4	Black Plastic Shell 黑色塑胶外壳	PCS	1
3	1.27mm 10P Gray 1.27mm 10P灰色	PCS	1
2	Hexagon Nuts & Screw 配套六角螺母螺钉	PCS	2
1	IDC2.54 10P Black IDC2.54 10P黑色	PCS	1
序号	Specification 品名规格	单位 unit	Qty 用量
D-SUB 9 Pins in Blue Male Jack connecting w/ 260mm long cable		UL0.2103.091	
标记	处数	更改文件号	签字 日期
设计	马杰	2010.05.09	
审核	冯燕锦	2010.05.10	
工艺	潘风	2010.05.11	
标准化	王海涛	2010.05.12	
批准	廖兴平	2010.05.14	
IDC10-VGA9-260		共1张	第1张