


取付穴参考寸法
MOUNTING HOLE DIMENSION



仕様 SPECIFICATION			
定格 RATING		DC12V 1A	12V DC 1A
耐電圧 DIELECTRIC STRENGTH		AC250V 1分間	250VAC FOR ONE MINUTE
絶縁抵抗 INSULATION RESISTANCE		DC500Vにて100MΩ以上	100MΩ MIN. AT DC500V
接触抵抗 CONTACT RESISTANCE		30mΩ以下	30mΩ MAX
挿入力 INSERTION FORCE		30N以下	30N MAX
抜去力 EXTRACTION FORCE		3~30N	3~30N

品番表			
品番 MODEL NO.		色 COLOR	
MR-565G0		赤 RED	
MR-565G1		黒 BLACK	
MR-565G2		緑 GREEN	
MR-565G5		青 BLUE	
MR-565G6		黄 YELLOW	
MR-565G7		白 WHITE	

LET	PART NAME	MATERIAL	QTY	FINISH	NOTE	TOLERANCE	SCALE	DATE	DESIG	DRAW	INSPE	APRO
7	ナット HEX, NUT	BSBM	1	Ni		±0.3	4/1	06/06/20	M. K	S. I	N. I	N. I
6	端子 TERMINAL	STEEL t=0.4	1	Ni								
5	ワッシャー WASHER	STEEL t=0.5	1	Ni								
4	コンタクト CONTACT	BSR	1	Au								
3	絶縁体B INSULATOR B	ABS	1									
2	絶縁体A INSULATOR A	ABS	1									
1	本体 BODY	BSBM	1	Au								
LET	PART NAME	MATERIAL	QTY	FINISH	NOTE							

TOLERANCE	SCALE	DATE	DESIG	DRAW	INSPE	APRO
±0.3	4/1	06/06/20	M. K	S. I	N. I	N. I
MODEL 型式		QTY	PART NAME 品名	No. MR-565G		
MATERIAL 材質				DRAW. NO 図番	MR565G-R	
FINISH 処理						