

# Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with spring-cage connection and D-Subminiature pin strip, for mounting on NS 35/7.5, 50-pos.

The illustration shows version UM 45-D 37SUB/S/ZFKDS

## Product Features

- 9 to 50-pos.
- Spring-cage connection technology
- According to IEC 60807-2
- 1:1 connection



## Key commercial data

package_quantity	1
GTIN	4017918120559

## Technical data

### Dimensions

Width	156 mm
Height	45 mm
Depth	50 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

### General

Nominal voltage $U_N$	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Max. current carrying capacity per branch	1.5 A (with even load on all branches)
Number of positions	50
Status display	No
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664

# Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

## Technical data

### General

Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV
Rated insulation voltage	125 V

### Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Spring-cage connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	1.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

### Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	50

## classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
-------------	----------

# Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

## classifications

### UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## approvals

---

GOST /

---

### Approval details



## accessories

### Screwdriver tools

SZF 0-0,4X2,5 - 1204504



## System cable

---

CABLE-D50SUB/B/S/ 50/KONFEK/S - 2302269



CABLE-D50SUB/B/S/100/KONFEK/S - 2302272



## Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

### accessories

CABLE-D50SUB/B/S/150/KONFEK/S - 2302285



CABLE-D50SUB/B/S/200/KONFEK/S - 2302298



CABLE-D50SUB/B/S/300/KONFEK/S - 2302308



CABLE-D50SUB/B/S/400/KONFEK/S - 2302311



CABLE-D50SUB/B/S/600/KONFEK/S - 2302324



CABLE D-SUB-S/.../.../... - 2302340



## Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

### accessories

---

CABLE D-SUB-B-B-S/.../.../... - 2302421



CABLE-D-50SUB/F/OE/0,25/S/0,5M - 2926292



CABLE-D-50SUB/F/OE/0,25/S/1,0M - 2926302



CABLE-D-50SUB/F/OE/0,25/S/1,5M - 2926315



CABLE-D-50SUB/F/OE/0,25/S/2,0M - 2926328



## Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

### accessories

CABLE-D-50SUB/F/OE/0,25/S/3,0M - 2926331



CABLE-D-50SUB/F/OE/0,25/S/4,0M - 2926344



CABLE-D-50SUB/F/OE/0,25/S/6,0M - 2926357




CABLE-D-50SUB-F-OE-0,25-S/... - 2900908



### Drawings

# Interface module - UM 45-D50SUB/S/ZFKDS - 2293653

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>