

## Protective covers - HC-B 6-TMS-SD-IP50 - 1690736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON ADVANCE IP50 protective cover B6, for panel mounting side, with clip locking, with retaining cord, diameter of retaining cord eyelet 3 mm

### Key commercial data

package_quantity	10
GTIN	4017918890629

### Technical data

#### Dimensions

Diameter of retaining cord eyelet	3.5 mm
-----------------------------------	--------

#### Ambient conditions

Degree of protection	IP50
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Design	B6
Type	HC-ADVANCE protective cover
Inflammability class according to UL 94	V0
Color	gray
Seal present	No

### classifications

#### eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27142104
eCl@ss 5.1	27142104
eCl@ss 6.0	27142104
eCl@ss 7.0	27142104
eCl@ss 8.0	27142104

#### ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040

# Protective covers - HC-B 6-TMS-SD-IP50 - 1690736

## classifications

### ETIM

<b>ETIM 4.0</b>	EC002040
<b>ETIM 5.0</b>	EC002040


### UNSPSC

<b>UNSPSC 6.01</b>	30212113
<b>UNSPSC 7.0901</b>	39121712
<b>UNSPSC 11</b>	39121712
<b>UNSPSC 12.01</b>	39121712
<b>UNSPSC 13.2</b>	39121712

## approvals

GOST /

### Approval details



## Drawings

### Dimensioned drawing

