

# Cable - CABLE-D25SUB/B/S/200/KONFEK/S - 2302159

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Round shielded cable set, with 25-pos. D-SUB female and male connectors, cable length: 2 m

The illustration shows a 15-position version

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918893118

## Technical data

### General

<b>Nominal voltage <math>U_N</math></b>	125 V AC/DC
<b>Max. current carrying capacity per path</b>	2 A
<b>Max. conductor resistance</b>	$\leq 0.09 \Omega/m$
<b>Length of cable</b>	2 m
<b>Single wire, cross section</b>	0.25 mm <sup>2</sup>
<b>AWG</b>	24
<b>External diameter</b>	10.5 mm
<b>Shielding</b>	yes
<b>Shielding</b>	Tinned copper-braided shield, approx. 85% covering
<b>Insertion/withdrawal cycles</b>	> 200

### Environmental conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 50 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C
<b>Flame resistance</b>	IEC 60332-1

### Connector, module side

<b>Number of positions</b>	25
<b>Connectors</b>	D-SUB socket strip
<b>Number of plugs</b>	1

### Connector, controller side

<b>Number of positions</b>	25
<b>Connectors</b>	D-SUB pin strip
<b>Number of plugs</b>	1

# Cable - CABLE-D25SUB/B/S/200/KONFEK/S - 2302159

## Technical data

### Supported controller

<b>Control</b>	ABB S800 I/O
- suitable I/O card	DI810
- suitable I/O card	DI811
- suitable I/O card	DI814
- suitable I/O card	DI830
- suitable I/O card	DI831
- suitable I/O card	DI840
- suitable I/O card	DI885
- suitable I/O card	DO810
- suitable I/O card	DO814
- suitable I/O card	DO840
- suitable I/O card	DP820
- suitable I/O card	AI810
- suitable I/O card	AI820
- suitable I/O card	AI830
- suitable I/O card	AI835
- suitable I/O card	AI845
- suitable I/O card	AO810
- suitable I/O card	AO820

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 2.0</b>	EC000237
<b>ETIM 3.0</b>	EC000237
<b>ETIM 4.0</b>	EC000237
<b>ETIM 5.0</b>	EC000830

### UNSPSC

<b>UNSPSC 6.01</b>	26121620
<b>UNSPSC 7.0901</b>	26121620
<b>UNSPSC 11</b>	26121620
<b>UNSPSC 12.01</b>	26121620
<b>UNSPSC 13.2</b>	26121620

# Cable - CABLE-D25SUB/B/S/200/KONFEK/S - 2302159

## approvals

---

UL Recognized / cUL Recognized / GOST / cULus Recognized /

---

### Approval details

UL Recognized 

cUL Recognized 

GOST 

cULus Recognized 

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>