

Connector - SACC-M 8MR-4CON-SH - 1436466

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator connector, connector, angled, 4-pos., M8, shielded, solder connection, metal knurl, cable diameter max. 5 mm

Product Features

- ✓ Safe use in the field, thanks to a high degree of protection
- ✓ Flexible: connectors for on-site assembly
- ✓ Reliable signal transmission - 360° shielding in environments with electromagnetic interference

Key commercial data

package_quantity	1
GTIN	4046356436380

Technical data

Dimensions

External diameter	3.5 mm ... 5 mm
Stripping length of the sheath	30 mm
Stripping length of the individual wire	3 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	30 V
Number of positions	4
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder connection
Conductor cross section	0.08 mm² ... 0.34 mm²
AWG conductor cross section	28 ... 22

Connector - SACC-M 8MR-4CON-SH - 1436466

Technical data

General

Insertion/withdrawal cycles	≥ 100
Torque	0.2 Nm (M8 knurl)
Assembly instructions	The connector pin assignment can be rotated 90° to the cable outlet

Material

Inflammability class according to UL 94	HB
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PUR / PA66
Material of grip body	Nickel-plated brass
Material, knurls	Nickel-plated brass
Sealing material	NBR

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27279221
eCl@ss 7.0	27440104
eCl@ss 8.0	27440104

ETIM

ETIM 3.0	EC002062
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST /

Approval details

Connector - SACC-M 8MR-4CON-SH - 1436466

approvals



accessories

Torque tool

TSD 02 SAC - 1208487



TSD-M 1,2NM - 1212224



Screwdriver tools

SACC BIT M8-D12 - 1208474



TSD-M SAC-BIT ADAPTER - 1212600



Protective cap

Connector - SACC-M 8MR-4CON-SH - 1436466

accessories

PROT-M 8 FS-PA-CHAIN - 1430857



Cable by the meter


SAC-4P-100,0-PUR/SH-0,25 - 1535794



Drawings

Connector - SACC-M 8MR-4CON-SH - 1436466


Dimensioned drawing



Plug M8 x 1, angled, shielded

Connector - SACC-M 8MR-4CON-SH - 1436466

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>