

# Technical datasheet: KPI-G2415-K8448

## Specifications:

Operating Temperature Range	-20°C to +60°C
Storage Temperature Range	-30°C to +70°C
Input Voltage	3 VDC to 18 VDC
Sound Pressure Level	85dB/ 12VDC/ 30cm
Max. Rated Current	12mA / 12VDC
Resonant Frequency	3.5 ± 0.5 KHz
Tone Nature	Continuous
Housing Material/Color	ABS/ Black

## Dimensions:

