

Cable gland - HC-M-KV-Z-M40 - 1646175

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Metal screw connection with strain relief clamp, thread length: 8 mm, cable sealing area: 24 - 33 mm, clamping area: 26 - 36 mm, SW 50, screw connection: M40

Key commercial data

package_quantity	10
GTIN	4017918941314

Technical data

Dimensions

Wrench size, union nut	52 mm
Wrench size, support	50 mm
External cable diameter	24 mm ... 33 mm
Conductor sealing range	24.00 mm ... 33.00 mm
Clamping range of the strain relief clip	26.00 mm ... 34.00 mm

Ambient conditions

Degree of protection	IP65
Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 80 °C

General

Cable gland material	Nickel-plated brass
Material, pressure screw	Nickel-plated brass
Cable seal material	Perbunan
Material, O-ring	NBR
Thread type on connection side	M40
Color	silver

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109

Cable gland - HC-M-KV-Z-M40 - 1646175

classifications

eCl@ss

eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Drawings

Cable gland - HC-M-KV-Z-M40 - 1646175

Dimensioned drawing

