

Technical datasheet: KPX-G1205A-K6394

Specifications:

Operating Temperature Range	-20°C to +70°C
Storage Temperature Range	-30°C to +80°C
Rated Voltage	5 VDC
Input Voltage	4 VDC to 8 VDC
Sound Pressure Level	85dB/ 5VDC/ 10cm
Max. Rated Current	30mA/ 5VDC
Resonant Frequency	2.3 ± 0.3 KHz
Tone Nature	Continuous
Housing Material/Color	PBT/ Black

Dimensions:

