

Technical datasheet: PCT-G1500-K8479

Specifications:

Operating Temperature Range	-20°C to +60°C
Storage Temperature Range	-30°C to +70°C
Capacitance at 100Hz	26 nF $\pm$ 30%
Sound Pressure Level	≥ 95 dB at 50Vp-p/ 3.5KHz/ 100cm
Max. Input Voltage	60Vp-p Square Wave
Housing Material/ Color	ABS/ Red

Dimensions:

