

Technical datasheet: KPCM-97H50U-47DB-1545

Specifications:

Operating Temperature Range	-20°C to +70°C
Storage Temperature Range	-20°C to +70°C
Sensitivity	-47 ± 3 dB (0dB= 1V/Pa, 1 KHz)
Sensitivity Reduction	-3 dB (f=1 KHz, 1 Pa)
Standard Operation Voltage	1.5 VDC
Max. Operation Voltage	10 VDC
Output Impedance	0.68 KΩ (f=1 KHz, 1 Pa)
Frequency	100 to 10000 Hz
Max. Current Consumption	0.5 mA (Vs=1.5 V, RL=0.68 KΩ)
Signal to noise ration	60 dBA (f=1 KHz, 1 Pa)
Housing Material	AL
Regulations	RoHS

Dimensions:

