

Disconnect terminal block - OTTA 6-T - 0790446

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Universal terminal block with bolt connection, with disconnect slide, cross section: 0.1 - 6 mm², width: 11 mm, color: Gray

Key commercial data

package_quantity	50
GTIN	4017918005559

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	36 A
Nominal voltage U _N	800 V (the nominal voltage applies to insulated cable lugs)
Open side panel	ja

Dimensions

Length	69 mm
Width	11 mm
Height NS 35/7,5	52 mm
Height NS 35/15	59.5 mm
Height NS 32	57 mm

Connection data

Conductor cross section solid min.	0.1 mm ²
Conductor cross section solid max.	6 mm ²

Disconnect terminal block - OTTA 6-T - 0790446

Technical data

Connection data

Conductor cross section stranded min.	0.1 mm ²
Conductor cross section stranded max.	6 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	10
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm
Connection method	Bolt connection
Connection in acc. with standard	DIN 46 234
Min. cross section	0.1 mm ²
Max. cross section	6 mm ²
Hole diameter	4.3 mm
Bolt diameter	4 mm
Connection in acc. with standard	DIN 46237
Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²
Hole diameter	4.3 mm
Bolt diameter	4 mm

classifications

eCl@ss

eCl@ss 4.0	27141126
eCl@ss 4.1	27141126
eCl@ss 5.0	27141126
eCl@ss 5.1	27141126
eCl@ss 6.0	27141126
eCl@ss 7.0	27141126
eCl@ss 8.0	27141126

ETIM

ETIM 2.0	EC000902
ETIM 3.0	EC000902
ETIM 4.0	EC000902
ETIM 5.0	EC000902

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Disconnect terminal block - OTTA 6-T - 0790446

approvals

CSA / UL Recognized / GOST / LR / GL / BV / GOST /

Approval details

CSA 	
Nominal voltage UN	600 V
Nominal current IN	25 A
mm²/AWG/kcmil	22-10

UL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	30 A
mm²/AWG/kcmil	

GOST 
--

LR

GL

BV



accessories

End cover

Disconnect terminal block - OTTA 6-T - 0790446

accessories

D-OTTA 6-T - 0790459



Screwdriver tools

SZS 1,0X6,5 VDE - 1205079



Bridge

EB 3-OTTA 6 - 3026036



EB 4-OTTA 6 - 3026049



EB 7-OTTA 6 - 3026052



Disconnect terminal block - OTTA 6-T - 0790446

accessories

EB 10- OTTA 6 - 0790420



EB 2- OTTA 6 - 0790608



Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



Disconnect terminal block - OTTA 6-T - 0790446

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Disconnect terminal block - OTTA 6-T - 0790446

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Disconnect terminal block - OTTA 6-T - 0790446

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Disconnect terminal block - OTTA 6-T - 0790446

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 10:UNBEDRUCKT - 1053001



UC-TM 10 - 0818069



UCT-TM 10 - 0829142



Labeled terminal marker

ZB 10 CUS - 0824941



Disconnect terminal block - OTTA 6-T - 0790446

accessories

UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Disconnect terminal block - OTTA 6-T - 0790446

accessories

E/UK - 1201442



E/UK 1 - 1201413



accessories

S-OTTA 6-T - 0311199


Drawings

Circuit diagram



Disconnect terminal block - OTTA 6-T - 0790446

Circuit diagram



a = open
1 = cover
2 = insertion bridge
4 = partition plate

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>