


仕様  
SPECIFICATION

耐電圧 : AC500V 1分間  
 DIELECTRIC STRENGTH:500V AC FOR ONE MINUTE.  
 接触抵抗 : 50mΩ以下  
 CONTACT RESISTANCE:50mΩ MAX  
 絶縁抵抗 : DC100Vにて100MΩ以上  
 INSULATION RESISTANCE:100MΩ MIN.AT 500V DC.

回路図

CIRCUIT



LET	PART NAME	MATERIAL	QTY	FINISH	NOTE
7	CAP	PE	1		
6	CONTACT D	BSR t=0.3	1	Ni	
5	CONTACT C	FAB-EH t=0.3	1	Ni	
4	CONTACT B	FAB-EH t=0.3	1	Au	
3	CONTACT A	FAB-EH t=0.25	1	Ni	
2	SLEEVE	BSR	1	Ni	
1	BODY	PA	1		

TOLERANCE	SCALE	DATE	DESIG	DRAW	INSPE	APRO
	4/1	14/12/15		M.K		

MODEL 型式	QTY	PART NAME 品名	4-CONDUCTOR SUB-MINIATURE IN-LINEJACK No. MJ068

MATERIAL 材質	DRAW. NO 図番	MJ068

FINISH 処理	FIG. NO