

Label sheet, DIN A4 - BMKL 27X18 SR - 0803689

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Label sheet, DIN A4, Sheet, silver, Unlabeled, Can be labeled with: Office printing systems, Mounting type: Adhesive, Lettering field: 27 x 18 mm

The figure shows a version of the article

Product Features

- ✓ These labels have been specially developed for laser printers
- ✓ The unperforated SK U ... sheets are available for custom label designs
- ✓ Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- ✓ Can be printed on all commercially available laser printers

Key commercial data

package_quantity	10
GTIN	4017918007645

Technical data

Dimensions

Length (b)	27 mm
Width (a)	18 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-20 °C ... 120 °C (Min.)
Ambient temperature (assembly)	> 5 °C
Recommended storage conditions	22 °C / 50 % relative humidity

General

Note	Print image may vary depending on laser printer
Color	silver
Base element material	Polyester
Components	Silicone-free
Material	Polyester
Number of individual labels	84
Number of individual labels per row	6
Adhesive	Acrylic
Printability	Office printing systems

Label sheet, DIN A4 - BMKL 27X18 SR - 0803689

Technical data

General

Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Salt spray testing result	Test passed
Alternating condensation climate with SO₂ test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	46 µm
Adhesive strength	29 µm

classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Label sheet, DIN A4 - BMKL 27X18 SR - 0803689

accessories


Printing system accessories

CMS-P1-PAD - 5144819



Drawings

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>