

Test plugs - PS-6/2,3MM RD - 3038736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Test plugs, Color: red

The figure shows the 5.2 mm wide version

Product Features

- ✓ Two-piece test plug for individual plug color combinations
- ✓ The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided

Key commercial data

package_quantity	10
GTIN	4017918904166

Technical data

Technical data

Color	red
Material	PA
Pitch	6 mm
Inflammability class according to UL 94	V0
Minimum temperature	-40 °C
Maximum temperature	125 °C

classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27141148

ETIM

ETIM 2.0	EC000897
----------	----------

Test plugs - PS-6/2,3MM RD - 3038736

classifications

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002255

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>