

Cover profile - APH-ME - 3034374

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cover profile carrier for mounting on NS 35/7.5 DIN rail for attaching the cover profile AP-ME

Product Features

- ✓ The APH-ME end bracket is used in conjunction with the AP-ME cover
- ✓ It offers parking options for FBS ...-8 plug-in bridges and can be sealed as an option

Key commercial data

package_quantity	10
GTIN	4046356316767

Technical data

Dimensions

Length (b)	138 mm
Height	69 mm
Width (a)	8.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	gray
Inflammability class according to UL 94	V2
Material	PA

classifications

eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143
eCl@ss 8.0	27141143

Cover profile - APH-ME - 3034374

classifications

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC002848

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>