



仕様
SPECIFICATION

耐電圧 : AC500V 1分間
 DIELECTRIC STRENGTH:500V AC FOR ONE MINUTE.
 接触抵抗 : 50mΩ以下
 CONTACT RESISTANCE:50mΩ MAX
 絶縁抵抗 : DC100Vにて100MΩ以上
 INSULATION RESISTANCE:100MΩ MIN.AT 500V DC.

LET	PART NAME	MATERIAL	QTY	FINISH	NOTE	TOLERANCE	SCALE	DATE	DESING	DRAW	INSPE	APRO
7	CABLE PROTECTOR	PVC				±0.3	2/1	06/5/1	K.S	N.I	K.S	M.K
6	CAP	BSBM	1	Ni								
5	SLEEVE TERMINAL	STEEL t=0.3	1	Ni		MODEL	QTY	PART NAME	3-CON.MINIATURE JACK			
4	TIP CONTACT	PBS t=0.25	1	Ni		型式		品名	No.MLR-033J			
3	RING CONTACT	PBS t=0.25	1	Au		MATERIAL		DRAW.NO	MLR033J			
2	BODY	PA	1			材質		図番				
1	SLEEVE METAL	BSBM	1	Ni		FINISH						
						処理						