


取付穴参考寸法
MOUNTING HOLE DIMENSION

仕様 SPECIFICATION		DC12V 1A	12V DC 1A
定格 RATING		DC12V 1A	12V DC 1A
耐電圧 DIELECTRIC STRENGTH		AC250V 1分間	250VAC FOR ONE MINUTE
絶縁抵抗 INSULATION RESISTANCE		DC500Vにて100MΩ以上	100MΩ MIN. AT DC500V
接触抵抗 CONTACT RESISTANCE		30mΩ以下	30mΩ MAX
挿入力 INSERTION FORCE		30N以下	30N MAX
抜去力 EXTRACTION FORCE		3~30N	3~30N



品番表		品番 MODEL NO.	色 COLOR
MR-565G0	赤 RED		
MR-565G1	黒 BLACK		
MR-565G2	緑 GREEN		
MR-565G5	青 BLUE		
MR-565G6	黄 YELLOW		
MR-565G7	白 WHITE		

LET	PART NAME	MATERIAL	QTY	FINISH	NOTE	TOLERANCE	SCALE	DATE	DESIG	DRAW	INSPE	APRO
7	ナット HEX, NUT	BSBM	1	Ni		±0.3	4/1	06/06/20	M. K	S. I	N. I	N. I
6	端子 TERMINAL	STEEL t=0.4	1	Ni								
5	ワッシャー WASHER	STEEL t=0.5	1	Ni								
4	コンタクト CONTACT	BSR	1	Au								
3	絶縁体B INSULATOR B	ABS	1									
2	絶縁体A INSULATOR A	ABS	1									
1	本体 BODY	BSBM	1	Au								

TOLERANCE	SCALE	DATE	DESIG	DRAW	INSPE	APRO
±0.3	4/1	06/06/20	M. K	S. I	N. I	N. I
MODEL 型式	QTY		PART NAME 品名	No. MR-565G		
MATERIAL 材質				DRAW. NO 図番	MR565G-R	
FINISH 処理						