

# Fork-type cable lug - C-FCI 1,5/M3,5 - 3240033

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Fork-type cable lug, red, 0.5 - 1.5 mm<sup>2</sup>, M3,5

## Product Features

- The fork-type cable lugs without plastic sleeve feature a hard-soldered neck. In conjunction with the CRIMPFOX-RC ... and CRIMPFOX-RCI ... pliers they can be used to achieve maximum conductor pull-out forces
- The insulated versions are halogen-free and feature "EASY ENTRY" technology

## Key commercial data

<b>package_quantity</b>	100
<b>GTIN</b>	4046356451109

## Technical data

### Dimensions

<b>Length (b)</b>	22 mm
<b>Width (a)</b>	5.7 mm
<b>Length of insulation sleeve (c)</b>	10.5 mm
<b>Inner dimension of the insulating collar (d)</b>	4.1 mm
<b>Inner diameter (f)</b>	3.7 mm
<b>Material thickness (g)</b>	0.75 mm

### General

<b>Color</b>	red
<b>Stripping length</b>	7 mm
<b>Components</b>	Halogen-free
<b>Inflammability class according to UL 94</b>	V2

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060701
<b>eCl@ss 4.1</b>	27060701
<b>eCl@ss 5.0</b>	27400201
<b>eCl@ss 5.1</b>	27400201
<b>eCl@ss 6.0</b>	27400201

## Fork-type cable lug - C-FCI 1,5/M3,5 - 3240033

### classifications

#### eCl@ss

eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

#### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052


#### UNSPSC

UNSPSC 6.01	27113201
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

### Drawings

## Fork-type cable lug - C-FCI 1,5/M3,5 - 3240033

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>