

Cover profile - APK 1 - 5022795

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Hinged cover profile, permits hinged covering of terminal strips when used with cover holder APK-TU and holding profile APK-HP; snaps into the holding profile APK-HP, dimensions: 95 x 50 mm

Product Features

- ☒ Can be labeled
- ☒ Protection against environmental influences
- ☒ Protection against accidental actuation of terminal points or disconnect terminal blocks
- ☒ Covering of live parts

Key commercial data

package_quantity	10
GTIN	4017918095291

Technical data

Dimensions

Length (b)	50 mm
Width (a)	95 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	transparent
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	Polycarbonate PC

classifications

eCl@ss

eCl@ss 4.0	23150301
eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143

Cover profile - APK 1 - 5022795

classifications

eCl@ss

eCl@ss 8.0	27141143
------------	----------

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC002498
ETIM 5.0	EC000886


UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Cover profile - APK 1 - 5022795

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>