

Branch terminal - AZK 35 - 0702997

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Branch terminal, Connection method Screw connection, Load current : 125 A, Cross section: 0.75 mm² - 35 mm², Width: 12 mm, Color: aluminum

Product Features

- ✓ It is often necessary to branch flat copper busbars in switchgear
- ✓ This can be done easily with the branch terminal block because the terminal block can later be attached and firmly clamped anywhere on a copper rail (up to max. 5 mm thick)

Key commercial data

package_quantity	10
GTIN	4017918003647

Technical data

General

Color	aluminum
-------	----------

General

Maximum load current	125 A (with 35 mm ² conductor cross section)
Nominal current I _N	125 A

Dimensions

Length	40 mm
Width	12 mm

Connection data

Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	35 mm ²
Conductor cross section stranded min.	0.75 mm ²
Conductor cross section stranded max.	35 mm ²
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	2
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	35 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.75 mm ²

Branch terminal - AZK 35 - 0702997

Technical data

Connection data

Conductor cross section stranded, with ferrule with plastic sleeve max.	35 mm ²
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	10 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	10 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	10 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	10 mm ²
Connection method	Screw connection
Stripping length	15 mm
Screw thread	M6
Tightening torque, min	3.2 Nm
Tightening torque max	3.7 Nm

classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141131
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Branch terminal - AZK 35 - 0702997

approvals

GOST / GOST /

Approval details



accessories

Screwdriver tools

SZS 1,0X6,5 VDE - 1205079



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>