

Marker sheet - SK U SR:UNGESTANZT - 0800145

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker sheet, Din A4, silver, Unlabeled, Can be labeled with: Plotter, Office printing systems, Mounting type: Adhesive, Lettering field: 296 x 210 mm

The figure shows a version of the article

Product Features

- ☒ The unperforated SK U ... sheets are available for custom label designs
- ☒ These labels have been specially developed for laser printers
- ☒ Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- ☒ Can be printed on all commercially available laser printers

Key commercial data

package_quantity	10
GTIN	4017918005757

Technical data

Dimensions

Length (b)	296 mm
Width (a)	210 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 150 °C

General

Note	Print image may vary depending on laser printer
Color	silver
Material	Polyester

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137

Marker sheet - SK U SR:UNGESTANZT - 0800145

classifications

eCl@ss

eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001675

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings