



| | |
|---|--------------|
| ITEM-NO. (ITEM-NO.) | 745-831 |
| Cross section1 (Cross section / mm²) | 0.2 - 6 |
| Cross section2 (Cross section / AWG) | 24 - 10 |
| Strip length (Strip length / mm) | 11 - 12 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 41 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 1 |
| Height (Height / mm) | 23 |
| Width (Width / mm) | 7.5 |
| Depth (Depth / mm) | 29.1 |
| No. of connection Points (No. of connection Points) | 1 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 4.76 |
| Dimensions (Dimensions) | 1,8 + 0,1 mm |