

File No	B/N	Sugo model no.	colour	Side	Wire	Break down (V)		current (mA)	Series Resistor		Life (h)	pcs/bag	size (mm x mm)/bag	G.W (kg) / bag
				ø x L (mm)	(mm)	AC	DC		110-120VAC	220-250VAC				
93013c822	720332	NE-2 4x10/30mm	Standard Brightenss	4 x 10	0.35 x 30	65	90	0.5	100	330	25000	500	103X118	0,097
93013c823	720346	NE-2 4x12/30mm	Standard Brightenss	4 x 12	0.35 x 30	65	90	0.5	100	330	25000	500	103X118	0,099
93013c824	720362	NE-2 4x16/30mm	Standard Brightenss	4 x 16	0.35 x 30	65	90	0.5	100	330	25000	500	103x118	0,1
93013c825	720061	NE-2 5x12/30mm	Standard Brightenss	5 x 12	0.4 x 30	65	90	0.5	100	330	25000	200	90X118	0,061
93013c827	720390	NE-2 5x16/30mm	Standard Brightenss	5 x 16	0.4 x 30	65	90	0.5	100	330	25000	200	103X118	0,078
93013c830	725686	NE-2 6x16/30mm	Standard Brightenss	6 x 16	0.4 x 30	65	90	0.5	100	330	25000	200	103X118	0,104
93013c831	725710	NE-2 6x18/30mm	Standard Brightenss	6 x 18	0.4 x 30	65	90	0.5	100	330	25000	200	103X118	0,113
93013c832	725727	NE-2 6x20/30mm	Standard Brightenss	6 x 20	0.4 x 30	65	90	0.5	100	330	25000	200	103X118	0,122
93013c833	725744	NE-2 6x22/30mm	Standard Brightenss	6 x 22	0.4 x 30	65	90	0.5	100	330	25000	200	130X135	0,135
93013c834	720259	NE-2UH 4x10/30mm	Ultra Brightness	4 x 10	0.35 x 30	95	135	1.5	33	100	25000	500	103X118	0,091
93013c835	720214	NE-2UH 5x12/30mm	Ultra Brightness	5 X 12	0.4 x 30	95	135	1.5	33	100	15000	200	90X118	0,059
93013c837	720272	NE-2UH 6x13/30mm	Ultra Brightness	6 X 13	0.4 x 30	95	135	2.0	22	68	15000	200	103X118	0,084
93013c838	720288	NE-2UH 6x16/30mm	Ultra Brightness	6 X 16	0.4 x 30	95	135	2.0	22	68	15000	200	103X118	0,106
93013c839	720154	NE-2UH 6x18/30mm	Ultra Brightness	6 X 18	0.4 x 30	95	135	2.0	22	68	15000	200	103X118	0,115
93013c840	720116	NE-2G 4x10/30mm	Green Brightness	4 x 10	0.35 x 30	85	120	0.5	100	330	20000	500	103X118	0,09
93013c841	720252	NE-2G 5x12/30mm	Green Brightness	5 x 12	0.4 x 30	85	120	0.7	82	220	15000	200	90X118	0,063
93013c843	720159	NE-2G 5x16/30mm	Green Brightness	5 x 16	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,078
93013c844	720181	NE-2G 6x12/30mm	Green Brightness	6 x 12	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,078
93013c846	720201	NE-2G 6x14/30mm	Green Brightness	6 x 14	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,08
93013c847	720215	NE-2G 6x16/30mm	Green Brightness	6 x 16	0.4 x 30	85	120	1.0	47	150	15000	200	103X118	0,099
93013c848	720190	NE-2G 6x18/30mm	Green Brightness	6 x 18	0.4 x 30	85	120	1.0	47	150	15000	200	103X118	0,11

93013c849	720000	NE-2W 4x10/30mm	White Brightness	4 x 10	0.35 x 30	85	120	0.5	100	330	15000	500	103X118	0,091
93013c850	720021	NE-2W 5x12/30mm	White Brightness	5 x 12	0.4 x 30	85	120	0.7	82	220	15000	200	90X118	0,061
93013c852	720040	NE-2W 6x12/30mm	White Brightness	6 x 12	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,087
93013c853	720058	NE-2W 6x14/30mm	White Brightness	6 x 14	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,08
93013c854	720076	NE-2W 6x16/30mm	White Brightness	6 x 16	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,1
93013c855	720097	NE-2W 6x18/30mm	White Brightness	6 x 18	0.4 x 30	85	120	0.8	68	180	15000	200	103X118	0,11
93013c856		NE-2B 4x10/30mm	Blue Brightness	4 x 10	0.35 x 30	85	120	0.5	100	330	10000	500	103X118	91
93013c857		NE-2B 5x13/30mm	Blue Brightness	5 x 13	0.4 x 30	85	120	0.7	82	220	10000	200	90X118	61
93013c858		NE-2B 6x12/30mm	Blue Brightness	6 x 12	0.4 x 30	85	120	0.8	68	180	10000	200	103X118	87
93013c859		NE-2B 6x14/30mm	Blue Brightness	6 x 14	0.4 x 30	85	120	0.8	68	180	10000	200	103X118	80
93013c860		NE-2B 6x16/30mm	Blue Brightness	6 x 16	0.4 x 30	85	120	0.8	68	180	10000	200	103X118	100
93013c861		NE-2B 6x18/30mm	Blue Brightness	6 x 18	0.4 x 30	85	120	0.8	68	180	10000	200	103X118	110
93013c862		NE-2B 6x20/30mm	Blue Brightness	6 x 20	0.4 x 30	85	120	1.0	47	150	10000	200	103X118	119