

CONRAD NR	model no.	colour	Side	Wire (mm)	Break down (V)		current (mA)	Series Resistor		Life (h)
			∅ x L (mm)		AC	DC		110- 120VAC	220- 250VAC	
720317	NE-2 3x13/30mm	Standard Brightenss	3.2 X 13	0.3 X 30	65	90	0.5	100	330	15000
720332	NE-2 4x10/30mm	Standard Brightenss	4 x 10	0.35 x 30	65	90	0.5	100	330	25000
720346	NE-2 4x12/30mm	Standard Brightenss	4 x 12	0.35 x 30	65	90	0.5	100	330	25000
720362	NE-2 4x16/30mm	Standard Brightenss	4 x 16	0.35 x 30	65	90	0.5	100	330	25000
720061	NE-2 5x12/30mm	Standard Brightenss	5 x 12	0.4 x 30	65	90	0.5	100	330	25000
720391	NE-2 5x13/30mm	Standard Brightenss	5 x 12	0.4 x 30	65	90	0.5	100	330	25000
720390	NE-2 5x16/30mm	Standard Brightenss	5 x 16	0.4 x 30	65	90	0.5	100	330	25000
	NE-2 6x12/30mm	Standard Brightenss	6 x 12	0.4 x 30	65	90	0.5	100	330	25000
	NE-2 6x13/30mm	Standard Brightenss	6 x 13	0.4 x 30	65	90	0.5	100	330	25000
725686	NE-2 6x16/30mm	Standard Brightenss	6 x 16	0.4 x 30	65	90	0.5	100	330	25000
725710	NE-2 6x18/30mm	Standard Brightenss	6 x 18	0.4 x 30	65	90	0.5	100	330	25000
725727	NE-2 6x20/30mm	Standard Brightenss	6 x 20	0.4 x 30	65	90	0.5	100	330	25000
725744	NE-2 6x22/30mm	Standard Brightenss	6 x 22	0.4 x 30	65	90	0.5	100	330	25000

720259	NE-2UH 4x10/30mm	Ultra Brightness	4 x 10	0.35 x 30	95	135	1.5	33	100	25000
720214	NE-2UH 5x12/30mm	Ultra Brightness	5 X 12	0.4 x 30	95	135	1.5	33	100	15000
	NE-2UH 5x13/30mm	Ultra Brightness	5 X 13	0.4 x 30	95	135	1.5	33	100	15000
720272	NE-2UH 6x13/30mm	Ultra Brightness	6 X 13	0.4 x 30	95	135	2.0	22	68	15000
720288	NE-2UH 6x16/30mm	Ultra Brightness	6 X 16	0.4 x 30	95	135	2.0	22	68	15000
720154	NE-2UH 6x18/30mm	Ultra Brightness	6 X 18	0.4 x 30	95	135	2.0	22	68	15000

720116	NE-2G 4x10/30mm	Green Brightness	4 x 10	0.35 x 30	85	120	0.5	100	330	20000
720252	NE-2G 5x12/30mm	Green Brightness	5 x 12	0.4 x 30	85	120	0.7	82	220	15000
	NE-2G 5x13/30mm	Green Brightness	5 x 13	0.4 x 30	85	120	0.7	82	220	15000
720159	NE-2G 5x16/30mm	Green Brightness	5 x 16	0.4 x 30	85	120	0.8	68	180	15000
720181	NE-2G 6x12/30mm	Green Brightness	6 x 12	0.4 x 30	85	120	0.8	68	180	15000
	NE-2G 6x13/30mm	Green Brightness	6 x 13	0.4 x 30	85	120	0.8	68	180	15000
720201	NE-2G 6x14/30mm	Green Brightness	6 x 14	0.4 x 30	85	120	0.8	68	180	15000
720215	NE-2G 6x16/30mm	Green Brightness	6 x 16	0.4 x 30	85	120	1.0	47	150	15000
720190	NE-2G 6x18/30mm	Green Brightness	6 x 18	0.4 x 30	85	120	1.0	47	150	15000

720000	NE-2W 4x10/30mm	White Brightness	4 x 10	0.35 x 30	85	120	0.5	100	330	15000
720021	NE-2W 5x12/30mm	White Brightness	5 x 12	0.4 x 30	85	120	0.7	82	220	15000
	NE-2W 5x13/30mm	White Brightness	5 x 13	0.4 x 30	85	120	0.7	82	220	15000
	NE-2W 6x12/30mm	White Brightness	6 x 12	0.4 x 30	85	120	0.8	68	180	15000
720058	NE-2W 6x14/30mm	White Brightness	6 x 14	0.4 x 30	85	120	0.8	68	180	15000
720076	NE-2W 6x16/30mm	White Brightness	6 x 16	0.4 x 30	85	120	0.8	68	180	15000
720097	NE-2W 6x18/30mm	White Brightness	6 x 18	0.4 x 30	85	120	0.8	68	180	15000