





**HEADER (FOR PRINTED CIRCUIT
BOARDS) STRAIGHT SOLDER PIN,
1X1 MM / 0.039X 0.039 IN PIN
SPACING 5 mm / 0.197 in Reflow-
technique**

231-132/001-000/105-604 TO 231-142/
001-000/105-604

ITEM-NO. (ITEM-NO.)	231-133/001-000/105-604
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	3
Height (Height / mm)	12
Width (Width / mm)	18.2
Depth (Depth / mm)	8.4
COLOR (COLOR)	schwarz
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3,2 mm
Dimensions (Dimensions)	1,4 +0,1 mm