





**MALE CONNECTOR WITH STRAIGHT  
LONG CONTACT PINS PIN SPACING 5  
MM / 0.197 IN 1.2x1.2 MM**  
231-162/003-000 TO 231-180/003-000

<b>ITEM-NO. (ITEM-NO.)</b>	231-164/003-000
<b>Measured voltage (Measured voltage / V)</b>	250
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	16
<b>RM (PIN SPACING / mm)</b>	5
<b>P (NO. OF POLES)</b>	4
<b>Height (Height / mm)</b>	12
<b>Width (Width / mm)</b>	23.2
<b>Depth (Depth / mm)</b>	8.4
<b>COLOR (COLOR)</b>	grau
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 3,2 mm