



**HEADER STRAIGHT SOLDER PIN, 1.2
X 1.2 MM /0.047 X 0.047 IN WITH
FIXING FLANGE PIN SPACING 5 MM /
0.197 IN
231-162/162-040 TO 231-174/040-000**

ITEM-NO. (ITEM-NO.)	231-174/040-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	14
Height (Height / mm)	12
Width (Width / mm)	82.8
Depth (Depth / mm)	8.4
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	6.942
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3,2 mm
Dimensions (Dimensions)	1,7 +0,1 mm