





**HEADER STRAIGHT SOLDER PIN, 1.2
X 1.2 MM /0.047 X 0.047 IN PIN
SPACING 5 MM / 0.197 IN
231-162/001-000 TO 231-184/001-000**

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 231-176/001-000 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 16 |
| RM (PIN SPACING / mm) | 5 |
| P (NO. OF POLES) | 16 |
| Height (Height / mm) | 12 |
| Width (Width / mm) | 83.2 |
| Depth (Depth / mm) | 8.4 |
| COLOR (COLOR) | grau |
| Comment (Comment) | L = (No. of poles x Pin Spacing) + 3,2 mm |
| Dimensions (Dimensions) | 1,7 +0,1 mm |