





**2-CONDUCTOR SPRING CLAMPS
WITH LOCKING LEVER PIN SPACING
5 MM / 0.197 IN
231-2102/037-000 TO 231-2116/037-000**

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 231-2107/037-000 |
| Cross section1 (Cross section / mm²) | 0.2 - 2.5 |
| Cross section2 (Cross section / AWG) | 24 - 12 |
| Strip length (Strip length / mm) | 9 - 10 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 16 |
| RM (PIN SPACING / mm) | 5 |
| P (NO. OF POLES) | 7 |
| Height (Height / mm) | 20.8 |
| Width (Width / mm) | 51.55 |
| Depth (Depth / mm) | 29.8 |
| No. of connection Points (No. of connection Points) | 14 |
| No. of potentials (No. of potentials) | 7 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 17.651 |
| Comment (Comment) | $L = (\text{No. of poles} - 2) \times \text{Pin Spacing} + 10 \text{ mm}$ |