





**2-CONDUCTOR SPRING CLAMPS
WITH LOCKING LEVER PIN SPACING
5 MM / 0.197 IN
231-2102/037-000 TO 231-2116/037-000**

ITEM-NO. (ITEM-NO.)	231-2112/037-000
Cross section1 (Cross section / mm²)	0.2 - 2.5
Cross section2 (Cross section / AWG)	24 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	12
Height (Height / mm)	20.8
Width (Width / mm)	76.55
Depth (Depth / mm)	29.8
No. of connection Points (No. of connection Points)	24
No. of potentials (No. of potentials)	12
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	29.116
Comment (Comment)	$L = (\text{No. of poles} - 2) \times \text{Pin Spacing} + 10 \text{ mm}$