



ITEM-NO. (ITEM-NO.)	231-2311/026-000
Cross section1 (Cross section / mm²)	0.2 - 2.5
Cross section2 (Cross section / AWG)	24 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	11
Height (Height / mm)	20.8
Width (Width / mm)	55.72
Depth (Depth / mm)	26.45
No. of connection Points (No. of connection Points)	22
No. of potentials (No. of potentials)	11
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	25.133
Comment (Comment)	L = (No. of poles - 2) x Pin Spacing) + 10 mm