



**HEADER (FOR PRINTED CIRCUIT BOARDS) STRAIGHT SOLDER PIN, 1. 2X1.2 MM / 0.047X 0.047 IN PIN SPACING 7.5 mm / 0.295 in Reflow-technique**

231-262/001-000/105-604 TO 231-272/001-000/105-604

<b>ITEM-NO. (ITEM-NO.)</b>	231-266/001-000/105-604
<b>Measured voltage (Measured voltage / V)</b>	630
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	7.5
<b>P (NO. OF POLES)</b>	6
<b>Height (Height / mm)</b>	12
<b>Width (Width / mm)</b>	45.7
<b>Depth (Depth / mm)</b>	8.4
<b>COLOR (COLOR)</b>	schwarz
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 8,2 mm
<b>Dimensions (Dimensions)</b>	1,7 +0,1 mm