



**HEADER (FOR PRINTED CIRCUIT
BOARDS) STRAIGHT SOLDER PIN, 1.
2X1.2 MM / 0.047X 0.047 IN PIN
SPACING 7.5 mm / 0.295 in Reflow-
technique**

231-262/001-000/105-604 TO 231-272/
001-000/105-604

ITEM-NO. (ITEM-NO.)	231-270/001-000/105-604
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	10
Height (Height / mm)	12
Width (Width / mm)	75.7
Depth (Depth / mm)	8.4
COLOR (COLOR)	schwarz
Comment (Comment)	L = (No. of poles x Pin Spacing) + 8,2 mm
Dimensions (Dimensions)	1,7 +0,1 mm