





**2-CONDUCTOR SPRING CLAMPS
WITH LOCKING LEVER PIN SPACING
7.62 MM / 0.3 IN
231-2702/037-000 TO 231-2716/037-000**

ITEM-NO. (ITEM-NO.)	231-2707/037-000
Cross section1 (Cross section / mm²)	0.2 - 2.5
Cross section2 (Cross section / AWG)	24 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	7
Height (Height / mm)	20.8
Width (Width / mm)	67.15
Depth (Depth / mm)	29.8
No. of connection Points (No. of connection Points)	14
No. of potentials (No. of potentials)	7
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	21.301
Comment (Comment)	L = (No. of poles - 2) x Pin Spacing) + 12.5 mm