



ITEM-NO. (ITEM-NO.)	231-2709/026-000
Cross section1 (Cross section / mm²)	0.2 - 2.5
Cross section2 (Cross section / AWG)	24 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	9
Height (Height / mm)	20.8
Width (Width / mm)	65.84
Depth (Depth / mm)	26.45
No. of connection Points (No. of connection Points)	18
No. of potentials (No. of potentials)	9
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	25.327
Comment (Comment)	$L = (\text{No. of poles} - 2) \times \text{Pin Spacing} + 12.5$ mm